

Übersicht	Kanäle	Einstellungen								
17	19	64QAM	714	0.0	-37.3	0.32	3	0		
18	20	64QAM	722	0.5	-37.6	0.32	6	0		
19	21	64QAM	730	1.0	-37.3	0.32	3	0		
20	22	64QAM	738	1.2	-37.6	0.32	0	0		
21	23	64QAM	746	1.5	-37.6	0.32	4	0		
22	24	64QAM	754	1.7	-38.6	0.32	7	0		
23	25	64QAM	762	1.1	-37.6	0.32	0	0		
24	26	64QAM	770	1.3	-37.6	0.32	0	0		
25	27	64QAM	778	1.8	-38.9	0.32	4	0		
26	28	64QAM	786	2.2	-38.6	0.32	3	0		
27	29	64QAM	794	2.2	-37.6	0.32	4	0		
28	30	64QAM	802	2.7	-38.6	0.32	5	0		
29	31	64QAM	810	2.3	-38.9	0.32	0	0		
30	32	64QAM	818	2.4	-38.9	0.32	3	0		
31	33	64QAM	826	2.6	-38.9	0.32	5	0		
32	34	64QAM	834	2.3	-38.9	0.32	6	0		